

intermediate chamber cloth / sleeve



SPECIFICATIONS

FABRIC

100 % MagiCloth™ INTERMEDIATE CHAMBER

TECHNICAL FEATURES

grammage: 180 g/m²

type: 100 % PES HACCP

DIMENSIONS

customised: according to the model of your device

CERTIFICATES

HACCP, IFS, FDA, certificate of suitability, maintenance instructions

COLOUR CARD

white colour

WASHING THE PRODUCT BEFORE FIRST USE

yes

WASHING TEMPERATURE RANGE

pre-washing: 30 - 40 °C

main washing: maximum 60 °C

USE OF PROTEIN DEGRADATION ENZYMES DURING WASHING

yes

SOAKING PREPARATIONS AND LAUNDRY DETERGENTS

odourless, according to HACCP guidelines

PREDICTED SHRINKAGE

technical fabric: 1 % (considered in the product)

IRONING

not necessary

DRYING

at low temperatures



UV-stabilised fabric

longer lifespan (at least 3 years)



washable fabric (60°C)

use of protein degradation enzymes during washing is permitted



breathable fabric

prevents temperature shock in the event of large temperature



durable fabric

more than 300 wash cycles



dimensionally stabilised fabric

fixed cover dimension



prevents the formation of microbes and mould

follows HACCP, IFS, FDA guidelines



reduces the absorption of moisture

breathable fabric prevents condensation




has a beneficial effect on the dough

allows the product to proof without any condensation or rapid drying issues



the design can be customised

cloths/sleeves are made according to the specifications of the machine



description and use

EASY HANDLING

The **MagiCloth™ INTERMEDIATE CHAMBER** fabric reduces the risk of microbiological contamination and provides optimal conditions for the dough to proof.

- Reduces the need to apply flour or starch to the cloth/sleeve
- Material is adapted to chamber conditions
- Allows for a faster drying of the cloth/sleeve
- Provides suitable proofing conditions
- Ensures a long service life (at least 3 years) with proper maintenance
- Easy handling, quick disassembly and assembly
- Use of protein degradation enzymes during washing is permitted
- Simple maintenance
- Guaranteed professional washing and service

All cloths/sleeves are manufactured in accordance with the requirements and wishes of the client, taking into account the chamber model, the dimensions of the basket and the method of attachment. Fastening straps (Velcro) may also be sewn onto the cloth or sleeve. The model with Velcro straps allows for a faster fabric handling and provides for a faster assembling and disassembling of cloths.

All products are equipped with an inset label that enables traceability throughout the production process.

The fabric is dimensionally stabilised and provides for a minimal shrinkage, which is taken into account during the manufacturing process. Washing takes place according to a predetermined procedure. Maintenance instructions are included. The product is accompanied by a declaration of conformity.




CUSTOM-MADE

Measurement key:

- A** – width of the cloth/sleeve
- B** – length of the cloth
- C** – length of the sleeve

To accurately fit the cloth/sleeve, measurements are performed at your location. If this is not possible, we will need a technical sketch of the basket with exact dimensions.

cloth



sleeve

